
# RING SEAL FLANGED BOLT-THRU

The Reotemp Ring Seal Flanged Bolt-thru boasts an In-Line Flow-Thru design ideal for waste water, slurries, or abrasives. Mounted between pipe flanges or threaded in-line, it has a tough but sensitive elastomer lining. One unique feature of this seal is the ability to mount multiple instruments on one seal.



SPECIFICATIO	NS							
Materials Boo	ly: Carbon St	eel, 316 SS						
Dia	End Flange: Carbon Steel, 316 SS. Diaphragm/Sleeve: Buna-N, PTFE EPDM, Natural Rubber and more.							
Process		Sleeve Material	Limit					
Temperature Limits		Buna-N	225°F					
		Viton	400°F					
		PTFE	350°F					
		EPDM	300°F					
		Natural Rubber	212°F					
	ME B16.5 Cla	ss 150# or 300	#					
Ambient Temperature Limits Det	ermined by th	ne pressure inst	rument					
Wetted Materials	Enc	l Flanges	Max Size					
End Flanges	Liic	316I						
	Car	Carbon Steel						
		Hastelloy C-276						
		itanium	4"					
	A	lloy 20	4"					
	Kyr	nar (VDF	4"					
	PTFE (25	% Glass Filled)	4"					
		PVC	4"					
All Non-Metallic End Flanges Rated to 150 PSIG Max		CPVC	4"					
Diaphragm/Sleeve								
Diapinaginoiceve	Е	Buna N	10"					
	\	/iton A	10"					
		PTFE	10" (2" min)					
	ı	EPDM	10"					
	Natu	Natural Rubber						

# RING SEAL FLANGED BOLT-THRU




ANSI ASME Class	Nom Pipe Size (in)	Inner Dia. B (in)	Outer Dia. A (in)	Width C (in)	Bolt Circle BC (in)	Bolt Dia. BD (in)	No. of Bolt Holes	Approx. Weight (lbs)
	1	1.05	4.25	2.00	3.12	0.625	4	5.7
	1.5	1.61	5.00	2.00	3.88	0.625	4	7.9
	2	2.07	6.00	2.00	4.75	0.75	4	12.0
	3	3.07	7.50	2.00	6.00	0.75	4	18.4
150	4	4.03	9.00	1.50	7.50	0.75	8	18.6
	5	5.05	10.00	1.50	8.50	0.88	8	21.0
	6	6.07	11.00	1.50	9.50	0.88	8	23.9
	8	7.98	13.50	1.50	11.75	0.88	8	34.5
	10	10.02	16.00	1.50	14.25	1.00	12	44.5
	2	2.07	6.50	2.00	5.00	0.75	8	13.8
	3	3.07	8.25	2.00	6.62	0.88	8	22.0
	4	4.03	10.00	1.50	7.88	0.88	8	24.5
300	5	5.05	11.00	1.50	9.25	0.88	8	32.0
	6	6.07	12.50	1.50	10.62	0.88	12	34.9
	8	7.98	15.00	1.50	13.00	1.00	12	47.1
	10	10.02	17.50	1.50	15.25	1.13	16	58.8

Custom dimensions are available if your application requires. Choose -CD as option code. Alternate manufacturers dimensions may differ from above.

	Liner/Sleeve Selection Chart											
Sleeve Material	Chemical Resistance	Max Temp.	Durability/Abrasion									
Buna N	Most common in Wastewater market. Limited chemical compatability.	225°F	Is an industry standard material that carries a medium/low abrasion resistance.									
Viton	Good chemical resistance that can be utilized in many applications. Limited chemical compatability.	400°F	Offers the best combination of temperature and high abrasion resistance.									
EPDM	Medium level of chemical resistance. Specialized material that performs very well in specific process medias.	300°F	Offers medium abrasion resistance.									
Natural Rubber	Often used in mining applications due to excellent wear properties, however, contains poor resistance to a variety of chemicals. Specialized material that performs very well in specific process medias.	212°F	Offers the highest resistance to abrasion out of the materials listed. NR is a tough material with a high durometer and stiffness.									
PTFE	Offers the best chemical resistance of all listed liners.	350°F	Soft material subject to plastic deformation and cold flow. Very low resistance to abrasion.									

## RING SEAL FLANGED BOLT-THRU




## SMART TRANSMITTER ATTACHMENT



## **DIFFERENTIAL PRESSURE ASSEMBLY**


Balanced System A complete assembly with one part number that includes two diaphragm seals, two capillaries, two fills, and one complete assembly calibration certificate.

Unbalanced DP System Where seal, mount, capillary, or fill is not identical. A complete assembly includes one diaphragm seal on the HP side AND one diaphragm seal on the LP side.





Mount via Process Connections High Pressure



Mount via Face of Cover Flange High Pressure Side



Mount via Process Connections Low Pressure




Cover Flange Low Pressure Side

### **GAUGE PRESSURE ASSEMBLY**

#### In Line Pressure Transmitter



Mount to In-Line Gauge -R1 Pressure Transmitter. Direct or remote mount



Horizontal Mount (Tank Mount) to In-Line Gauge Pressure Transmitter. Direct mount only.

Traditional Mount for Gauge Pressure Seal mount on one side only, other side is vented.

-R2



Instrument mount through process connections. HP Side. Use "R3" if mounting to




Instrument mount through face of cover flange, HP Side. Use "R9" if mounting to LP

55 (800) 648-7737 sales@reotemp.com PTC-1021 reotemp.com

## DIAPHRAGM SEAL ASSEMBLY TO SMART TRANSMITTERS

Reotemp specializes in the unique craft of assembling diaphragm seals to field transmitters for the purpose of measuring pressure, differential pressure, level, and flow. As a trusted supplier to many of the world's leading transmitter manufacturers, Reotemp can assemble a diaphragm seal system to virtually any make or model transmitter. Every transmitter mount includes the features below to ensure superior performance and durability for every assembly. Reotemp also offers repair, refurbishment or replacement of used transmitters with remote seals.



# Diaphragm Seals

## INSTRUMENT MOUNTING CONFIGURATIONS

#### **DIRECT MOUNT**

Direct Mounting a pressure gauge, switch, or transmitter is the most common diaphragm seal assembly.



- Allows Replaceability
- High Quality Thread Sealant
- Inspector Seal




- **Tamper Proof**
- Rated for High Temps
- Leak Resistant

Code	Description	Max. Temp
-DTD	Threaded Instrument Connection	400°F
-DWD	Welded Instrument Connection	600°F

Assembly Notes: Welded connection recommended for pressure exceeding 1,500 psi for purposes of leak prevention.

## **COOLING ELEMENTS**

Used in either high temp or cold temp applications, Cooling Elements mounted above diaphragm seals quickly normalize fluid temperature toward ambient. This protects the pressure instrument while still maintaining the convenience of a direct mount.




Code	Description	Max. Temp
-RTR	6" Cooling Tower	750°F
-STW	3" Cooling Standoff	600°F

Assembly Notes: Cooling elements are welded to diaphragm seal. Instruments are threaded to cooling element unless specified. All lengths are nominal.

### **REMOTE MOUNT**

Remote Mounting a pressure instrument using flexible capillary is a common mounting method when the point of measurement is in a hazardous or inconvenient location.




Code	Description	Max. Temp
-P??	PVC Coated SS Armor, Threaded to Seal	400°F
-W??	PVC Coated SS Armor, Welded to Seal	600°F
-A??	SS Flexible Armor, Threaded to Seal	400°F
-B??	SS Flexible Armor, Welded to Seal	750°F
Note: ?? =	Length in feet (e.g. 05 = 5 feet)	

Assembly Notes: Capillary has a 2mm inner diameter unless specified differently by customer. Ambient temp limit of PVC coated armor is 250°F. Standard instrument connection is threaded (Smart Transmitters are welded), unless specified by customer.

### TREE ASSEMBLIES

Tree Assemblies offer the ability to mount two pressure instruments onto one diaphragm seal, allowing the user to gain both a local indication and a remote signal without adding an additional pipe insertion.



Code	Description	Max. Temp
-TRE	Goal Post, Low Pressure Assembly (Max. 150 psi)	400°F
-TRX	Goal Post, Heavy Duty (Max. 3,000 psi)	600°F
-TRM	Compact Tree Assembly (Max. 3,000 psi)	600°F

Assembly Notes: Threaded joints are fully welded for consistent instrument orientation. Instrument connections are threaded unless specified by customer. Diaphragm seal must displace enough fluid to drive both instruments.

# Diaphragm Seals

# **FILL GUIDE**

Diaphragm seals are designed to protect pressure instruments from hot process media and corrosive chemicals while minimizing any negative effect on instrument accuracy and durability. A well-made diaphragm seal can achieve this goal only if it is properly assembled, filled, and tested. Reotemp's highly trained technicians use state-of-the-art equipment so that every diaphragm seal assembly is filled and tested to assure optimal instrument performance:

- ✓ 24-hour Minimum Fluid Degassing
- ✓ Evacuated Instrument
  Chamber Up to
  10<sup>-8</sup> mbar Absolute
- ✓ Complete Fill Integrity Check
- √ Fill-port Leak Test
- ✓ Post-fill Static Test
- ✓ Verification of Instrument
- ✓ High-temp Pipe Sealant
  Used on All Threaded Joints
- (Welded Joints Upon Request)
- ✓ Tamper-proof (Inspection Seal) Lacquer used on All Threaded Joints
- Sturdy Diaphragm Packaging Protection



Part Number Code	Name	Description	Temperature Range (Vacuum Service <5psia)	<b>Pulse</b> +™	Viscosity cst @ ~77°F	Specific Gravity @ ~77°F	Thermal Expansion cc/cc/°C
		STANDARD FILL FLUID					
AS	Silicone DC200 <sup>1</sup>	This is the standard fill fluid for most diaphragm seal applications.	-40°F to 400°F (-40°F to 250°F)	Yes	20	0.94	.00104
		HIGH TEMP SILICONE					
ВН	Silicone DC704 <sup>1</sup>	Standard for Smart Transmitters and capillary systems. Performs well in applications with high temperature and a deep vacuum.	0°F to 650°F (0°F to 450°F)	No	44	1.07	.00077
B1	Silicone DC710 <sup>1</sup>	Highest temperature rating; ideal for gauge seal assemblies. Too thick for capillary assemblies. Response time can become very slow in cold conditions.	50°F to 750°F (50°F to 400°F)	Yes	500	1.11	.00043
C8	Syltherm 800 <sup>2</sup>	Low viscosity allows it to perform well in both low and high temperatures. Not recommended for vacuum service or at high temperatures when under low static pressure.	-40°F to 750°F (-40°F to 150°F)	No	9.5	0.93	.00136
B5	Silicone DC705 <sup>1</sup>	Performs very well in high temperatures when under vacuum. The high viscosity and freezing point of this fluid makes it a poor choice for cold or outdoor installations without heat tracing.	50°F to 675°F (50°F to 550°F)	Yes	175	1.09	.00096
B2	Silicone DC550 <sup>1</sup>	Similar high temperature performance as DC705, however it performs better at lower temperatures.	-40°F to 575°F (-40°F to 400°F)	No	125	1.07	.00076
		FOOD GRADE					
AG	Glycerin USP	This is the standard fill fluid for most gauge seal assemblies for food, beverage, and pharmaceutical applications. Its high viscosity will cause very slow response at times in low temperature and outdoor installations.	60°F to 450°F (Not Suitable)	Yes	1100	1.26	.00061
BN	NEOBEE M20 <sup>7</sup>	Low viscosity and a wide temperature range makes this the standard sanitary fill fluid for Smart Transmitters and capillary systems.	-10°F to 400°F (-10°F to 200°F)	No	10	0.92	.00101
BS	Food Grade Silicone	Highest temperature limit for food grade fluids. Because of its high viscosity it does not perform well in low temperatures.	20°F to 550°F (20°F to 250°F)	Yes	350	0.97	.00096
ВР	Propylene Glycol	This is the fill fluid used when Glycol is called for on the customer specification. It has a very narrow temperature range.	0°F to 200°F (Not Suitable)	No	2.85	1.03	.00073
	- 1	NERT (TYPICALLY FOR CHLORINE AND OXYGEN APPLICATIONS	OR IN SILICONE-	FREE ENVI	RONMENTS	S)	
C1	Fomblin Y06 <sup>4</sup>	Ideal inert fluid for transmitter applications. Relatively high vapor pressure above 200°F. Not recommended for use in high temperature situations with low static pressure.	-40°F to 450°F (0°F to 250°F)	No	71	1.88	.00086
C2	Halocarbon 6.3 <sup>3</sup>	Standard inert fluid used in gauge seal assemblies.	-40°F to 400°F (-40°F to 200°F)	Yes	6.3	1.87	.00084
C3	Halocarbon 1.8 <sup>3</sup>	Typically used in low temperature applications because of its low viscosity.	-110°F to 220°F (-100°F to 100°F)	No	1.8	1.82	.00084
C4	Fluorolube FS-5 <sup>5</sup>	Similar performance to Halocarbon 6.3, however not suitable for vacuum service.	-40°F to 450°F (Not Suitable)	No	5	1.86	.00087
		SPECIALTY					
СК	Krytox 1506 <sup>6</sup>	Specialty fill fluid, inert.	-40°F to 350°F (-40°F to 300°F)	No	62	1.88	.00095
BE	Ethylene Glycol	Occasionally used in annular (O-ring) seal assemblies.	-25°F to 320°F (Not Suitable)	No	30	1.10	.00062

<sup>1</sup> Trademark Dow Corning

Note: PulsePlus™ fill fluids may have different physical properties than specified. Chemical composition and temperature ranges do not vary.

<sup>3</sup> Trademark Halocarbon Product Corporation

<sup>5</sup> Trademark Hooker Chemical Company

<sup>7</sup> Trademark Stepan Specialty Products

<sup>2</sup> Trademark The Dow Chemical Company

<sup>4</sup> Trademark AUSIMONT S.P.A

<sup>6</sup> Trademark The Chemours Company FC, LLC

# Diaphragm Seals

## **DIAPHRAGM SEAL OPTIONS**



N/A Indicates the option is not available

- ✓ Check Stock
- ✓ Get Price
- ✓ Configure Part #
- ✓ Download PDF Data Sheets

		MS4 MS6 MS8	W5 W6 W7	T5 T6 V5	W9FF W9FR	W9XT	W9FP	DSTC75	DSTC15 AND LARGER	DSTF05	DSTF75 AND LARGER	OR	DXFR
PULSATION PROTECTION (ONLY AVAILABLE WITH REOTEMP PRESSURE GAUGE MOUNTED TO SEAL)													
-PP	Pulse Plus™	✓	✓	✓	✓	✓	N/A	N/A	✓	N/A	✓	✓	N/A
					DIAPHR	AGM CO	ATING						
-AU	Gold Plated Diaphragm	N/A	✓	N/A	✓	✓	✓	✓	✓	✓	✓	N/A	N/A
-TC	Teflon Coated Diaphragm PTFE	N/A	✓	N/A	✓	✓	✓	N/A	✓	N/A	✓	N/A	N/A
-EP	Electropolished Diaphragm	N/A	N/A	N/A	N/A	N/A	N/A	✓	✓	✓	✓	N/A	N/A
						FILL							
-FW	Fill Port Welded Closed	STD <sup>1</sup>	✓	✓	✓	✓	✓	✓	✓	✓	✓	N/A	N/A
-VF	Fill for Vacuum Service	N/A	✓	N/A	✓	✓	✓	N/A	✓	N/A	✓	N/A	N/A
					CLEANII	NG AND	FINISH						
-DG	Degreased, Shipped in Sealed Bag	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	N/A	✓
-ох	Cleaned for Oxygen Service per ASME B40.1	✓	✓	N/A	✓	✓	✓	✓	✓	✓	✓	N/A	✓
-OY	Cleaned for Oxygen Service per MIL-STD-1330D	✓	✓	N/A	✓	✓	✓	✓	✓	✓	✓	N/A	✓
				ı	PLUG FO	R FLUS	PORT						
-GS	1/4" SS Plug Installed	STD	STD	STD	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	✓
-JS	1/2" SS Plug Installed	N/A	STD	STD	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	✓
-GH	1/4" Hast C Plug Installed	✓	✓	✓	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	✓
-JH	1/2" Hast C Plug Installed	N/A	✓	✓	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	✓
-GM	1/4" Monel Plug Installed	N/A	✓	✓	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	✓
-JM	1/2" Monel Plug Installed	N/A	✓	✓	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	✓
					TA	G OPTIO	N						
-TS	Stainless Steel Tag (1-10 Characters)							✓					
-TM	Stainless Steel Tag (11-80 Characters)							✓					
-TP	Paper Tag							✓					
				C	ERTIFIC	ATION O	PTIONS						
-NC	Certificate of NACE Compliance	✓	✓	N/A	✓	✓	✓	N/A	N/A	✓	✓	N/A	✓
-CM	General Material Conformance	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
-MR	MTR - Mill Test Report Certificate	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	N/A	✓
-PM	PMI - Positive Material Identification Certificate	✓	✓	✓	✓	✓	✓	✓	<b>✓</b>	✓	✓	N/A	✓
-HT	Hydrostatic Test per ASME B31.3	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	N/A	N/A
-HL	Helium Leak Test Certificate	✓	✓	N/A	✓	✓	✓	✓	✓	✓	✓	N/A	N/A
✓ li	Indicates that the option is available  1 Standard on MS8, available on MS4 & M								4 & MS6.				