

ONE-PIECE FLANGED FLUSH FACE DIAPHRAGM SEAL

Reotemp's W9FF flanged flush-face seal is a one-piece, all-welded assembly. The diaphragm is integral with the flange, giving a crevice-free surface that keeps process flow sweeping across to prevent solids buildup. It is the most economical choice for 316 SS service, and can also be supplied in solid Hastelloy, Monel, Alloy 20, and other exotic alloys when enhanced corrosion resistance is required.



W9FF Wetted Flange





Weights and Dimensions:

	Flange Rating	Α	В	# of Bolts	Weight (lbs.)
1"		4.25"	.56"	4	2
1 ½"	150#	5"	.69"	4	4
2"		6"	.75"	4	5
3"		7.5"	.94"	4	9
4"		9"	.94"	8	17
1"		4.88"	.69"	4	4
1 ½"	300#	6.13"	.81"	4	7
2"		6.5"	.88"	8	8
3"		8.25"	1.13"	8	16

Maximum Working Pressures at 100°F:

Determined by ANSI B16.5 flange ratings.

NOTE: Weights and dimensions is for raised face flange only. Other flange sizes and sealing face info can be found in ANSI B16.5 standards.

FEATURES / BENEFITS

- · One-piece Seal Design Bolts Directly to Process Flange
- · Center or Side Instrument Exit
- · Commonly Supplied with Flush/Calibration Ring
- · Ideal for Gauge or Differential Pressure Transmitters

SPECIFICATIONS

Wetted Materials Flange: 316 SS, 304 SS, Monel, Alloy 20,

or Hast C-276.

Diaphragm: Identical to Flange Material

Process -150° to 850°F

Temperature Limits

Ambient Determined by the pressure instrument.

Temperature Limits

Minimum

Recommended Span	Diaphragm Size								
	1.3"	1.9"	2.2"	3.5"	4.1"				
2.5" & 3.5" Gauges	N/A	30 psi	15 psi	10 psi	30" H ₂ O				
4", 4.5", & 6" Gauges	N/A	60 psi	30 psi	10 psi	30" H ₂ O				
Transmitter (Gauge Pressure)	50 psi	15 psi	150" H ₂ O	30" H ₂ O	15" H ₂ O				
Transmitter (Differential Pressure)	20 psi	200" H ₂ O	100" H ₂ O	30" H ₂ O	15" H ₂ O				
Differential Pressure Gauge	N/A	N/A	N/A	N/A	100" H ₂ O				


Available Diaphragm Sizes

1"
Α
Α
Α
Α
D
D
-

ONE-PIECE FLANGED FLUSH FACE DIAPHRAGM SEAL

HOW TO ORDER: Choose options to build a part number. For example: W9FFWR21S-W10-AS-TS // DXFR241S





-XX = No Fill Fluid



PTC-0425 (800) 648-7737 142 reotemp.com


SMART TRANSMITTER ATTACHMENT



DIFFERENTIAL PRESSURE ASSEMBLY


Balanced System A complete assembly with one part number that includes two diaphragm seals, two capillaries, two fills, and one complete assembly calibration certificate.

Unbalanced DP System Where seal, mount, capillary, or fill is not identical. A complete assembly includes one diaphragm seal on the HP side AND one diaphragm seal on the LP side.





-RH Mount via Process Connections Side High Pressure



-RB Cover Flange
Side High Pressure



-RL Mount via Process Connections
Side Low Pressure



-RC Mount via Face of Cover Flange


Side Low Pressure

GAUGE PRESSURE ASSEMBLY

In Line Pressure Transmitter



Mount to In-Line Gauge
-R1 Pressure Transmitter.
Direct or remote mount.



Horizontal Mount (Tank Mount) to In-Line Gauge Pressure Transmitter. Direct mount only. **Traditional Mount for Gauge Pressure** Seal mount on one side only, other side is vented.

-R2



Instrument mount through process connections, HP Side. Use "R3" if mounting to LP side




Instrument mount through face of cover flange, HP Side. Use "R9" if mounting to LP Side

96 (800) 648-7737 reotemp.com PTC-0425

DIAPHRAGM SEAL ASSEMBLY TO SMART TRANSMITTERS

Diaphragm Seals


Reotemp specializes in the unique craft of assembling diaphragm seals to field transmitters for the purpose of measuring pressure, differential pressure, level, and flow. As a trusted supplier to many of the world's leading transmitter manufacturers, Reotemp can assemble a diaphragm seal system to virtually any make or model transmitter. Every transmitter mount includes the features below to ensure superior performance and durability for every assembly. Reotemp also offers repair, refurbishment or replacement of used transmitters with remote seals.



INSTRUMENT MOUNTING CONFIGURATIONS

DIRECT MOUNT

Direct Mounting a pressure gauge, switch, or transmitter is the most common diaphragm seal assembly.



- · Allows Replaceability
- High Quality Thread Sealant
- Inspector Seal




- Tamper Proof
- · Rated for High Temps
- Leak Resistant

Code	Description	Max. Temp
-DTD	Threaded Instrument Connection	400°F
-DWD	Welded Instrument Connection	600°F

Assembly Notes: Welded connection recommended for pressure exceeding 1,500 psi for purposes of leak prevention.

COOLING ELEMENTS

Used in either high temp or cold temp applications, Cooling Elements mounted above diaphragm seals quickly normalize fluid temperature toward ambient. This protects the pressure instrument while still maintaining the convenience of a direct mount.



Code	Description	Max. Temp
-RTR	6" Cooling Tower	750°F
-STW	3" Cooling Standoff	600°F

Assembly Notes: Cooling elements are welded to diaphragm seal. Instruments are threaded to cooling element unless specified. All lengths are nominal.

REMOTE MOUNT

Remote Mounting a pressure instrument using flexible capillary is a common mounting method when the point of measurement is in a hazardous or inconvenient location.




Code	Description
Α	Armored, Threaded, 2mm
В	Amored, Welded, 2mm
W	PVC, Threaded, 2mm
P	PVC, Welded, 2mm
С	Armored, Threaded, 1mm
E	Armored, Welded, 1mm
F	PVC, Threaded, 1mm
G	PVC, Welded, 1mm
Н	Armored, Threaded, 0.55mm
J	Armored, Welded, 0.55mm
K	PVC, Threaded, 0.55mm
L	PVC, Welded, 0.55mm
Note: ?? =	Length in feet (e.g. 05 = 5 feet)

Assembly Notes: 2mm, 1mm, and .55mm are capillary inner diameter. Ambient temperature limit of PVC coated armor is 250°F. Process temperature limit of threaded connections is 400°F. Standard instrument connection is threaded (Smart Transmitters are welded), unless specified by customer.

TREE ASSEMBLIES

Tree Assemblies offer the ability to mount two pressure instruments onto one diaphragm seal, allowing the user to gain both a local indication and a remote signal without adding an additional pipe insertion.



Code	Description	Max. Temp
-TRE	Goal Post, Low Pressure Assembly (Max. 150 psi)	400°F
-TRX	Goal Post, Heavy Duty (Max. 3,000 psi)	600°F
-TRM	Compact Tree Assembly (Max. 3,000 psi)	600°F

Assembly Notes: Threaded joints are fully welded for consistent instrument orientation. Instrument connections are threaded unless specified by customer. Diaphragm seal must displace enough fluid to drive both instruments.

Diaphragm Seals

FILL GUIDE

Diaphragm seals are designed to protect pressure instruments from hot process media and corrosive chemicals while minimizing any negative effect on instrument accuracy and durability. A well-made diaphragm seal can achieve this goal only if it is properly assembled, filled, and tested. Reotemp's highly trained technicians use state-of-the-art equipment so that every diaphragm seal assembly is filled and tested to assure optimal instrument performance:

- √ 24-hour Minimum Fluid De-gassing
- ✓ Evacuated Instrument Chamber Up to 10-8
 mbar Absolute
- ✓ Complete Fill Integrity Check
- √ Fill-port Leak Test
- ✓ Post-fill Static Test
- ✓ Verification of Instrument Calibration
- ✓ High-temp Pipe Sealant Option for Joints
- √ Tamper-proof (Inspection Seal) Lacquer used on All Threaded Joints
 - Sturdy Diaphragm Packaging Protection

Part Number Code	Name	Description	Temperature Range (Vacuum Service <5psia)	Pulse ^{+™}	Viscosity cst @ ~77°F	Specific Gravity @ ~77°F	Thermal Expansion cc/cc/°C				
		STANDARD FILL FLUID									
AS	Silicone DC200 ¹	This is the standard fill fluid for most diaphragm seal applications.	-40°F to 400°F (-40°F to 250°F)	Yes	20	0.94	.00104				
HIGH TEMP SILICONE											
ВН	Silicone DC704 ¹	Standard for Smart Transmitters and capillary systems. Performs well in applications with high temperature and a deep vacuum.	0°F to 650°F (0°F to 450°F)	No	44	1.07	.00077				
B1	Silicone DC710 ¹	Highest temperature rating; ideal for gauge seal assemblies. Too thick for capillary assemblies. Response time can become very slow in cold conditions.	50°F to 750°F (50°F to 400°F)	Yes	500	1.11	.00043				
C8	Syltherm 800 ²	Low viscosity allows it to perform well in both low and high temperatures. Not recommended for vacuum service or at high temperatures when under low static pressure.	-40°F to 750°F (-40°F to 150°F)	No	9.5	0.93	.00136				
B5	Silicone DC705 ¹	Performs very well in high temperatures when under vacuum. The high viscosity and freezing point of this fluid makes it a poor choice for cold or outdoor installations without heat tracing.	50°F to 675°F (50°F to 550°F)	Yes	175	1.09	.00096				
B2	Silicone DC550 ¹	Similar high temperature performance as DC705, however it performs better at lower temperatures.	-40°F to 575°F (-40°F to 400°F)	No	125	1.07	.00076				
		FOOD GRADE									
AG	Glycerin USP	This is the standard fill fluid for most gauge seal assemblies for food, beverage, and pharmaceutical applications. Its high viscosity will cause very slow response at times in low temperature and outdoor installations.	60°F to 450°F (Not Suitable)	Yes	1100	1.26	.00061				
BN	NEOBEE M207	Low viscosity and a wide temperature range makes this the standard sanitary fill fluid for Smart Transmitters and capillary systems.	-10°F to 400°F (-10°F to 200°F)	No	10	0.92	.00101				
BS	Food Grade Silicone	Highest temperature limit for food grade fluids. Because of its high viscosity it does not perform well in low temperatures.	20°F to 550°F (20°F to 250°F)	Yes	350	0.97	.00096				
ВР	Propylene Glycol	This is the fill fluid used when Glycol is called for on the customer specification. It has a very narrow temperature range.	0°F to 200°F (Not Suitable)	No	2.85	1.03	.00073				
	INE	RT (TYPICALLY FOR CHLORINE AND OXYGEN APPLICATIONS O	R IN SILICONE-I	FREE ENVIR	RONMENTS)					
C1	Fomblin Y06 ⁴	Ideal inert fluid for transmitter applications. Relatively high vapor pressure above 200°F. Not recommended for use in high temperature situations with low static pressure.	-40°F to 450°F (0°F to 250°F)	No	71	1.88	.00086				
C2	Halocarbon 6.3 ³	Standard inert fluid used in gauge seal assemblies.	-40°F to 400°F (-40°F to 200°F)	Yes	6.3	1.87	.00084				
C3	Halocarbon 1.8 ³	Typically used in low temperature applications because of its low viscosity.	-110°F to 220°F (-100°F to 100°F)	No	1.8	1.82	.00084				
C4	Fluorolube FS-5 ⁵	Similar performance to Halocarbon 6.3, however not suitable for vacuum service.	-40°F to 450°F (Not Suitable)	No	5	1.86	.00087				
		SPECIALTY									
СК	Krytox 1506 ⁶	Specialty fill fluid, inert.	-40°F to 350°F (-40°F to 300°F)	No	62	1.88	.00095				
BE	Ethylene Glycol	Occasionally used in annular (O-ring) seal assemblies.	-25°F to 320°F (Not Suitable)	No	30	1.10	.00062				
СТ	Syltherm XLT ²	Used for very low process temperatures.	-150°F to 500°F (Not Suitable)	No	1.4	0.85	.00168				

- 1 Trademark Dow Corning
- 3 Trademark Halocarbon Product Corporation
- 5 Trademark Hooker Chemical Company
- 7 Trademark Stepan Specialty Products

- 2 Trademark The Dow Chemical Company
- 4 Trademark AUSIMONT S.P.A
- 6 Trademark The Chemours Company FC, LLC

Note: PulsePlus™ fill fluids may have different physical properties than specified. Chemical composition and temperature ranges do not vary.

DIAPHRAGM SEAL ACCESSORIES

DRY CAPILLARY



- Used When Pressure Instrument Needs to be Removed from Direct Contact of Installation Point
- All-welded 316SS Construction
- Available up to 100 ft. in Length (Max Recommended Length of 40 ft. in DSS)
- Max Working Pressure of 10,000 psig (5,000 psig for 3mm ID) All Pressure Ratings are at 100°F
- 2mm ID Standard
- Note: if capillary is part of a filled diaphragm seal system use 3 digit mounting code per page 98 (Example: "A25" = 25' of armored capillary, threaded to seal)

HOW TO ORDER: Choose options to build a part number. For example: DXC4M4M10A-TS

DXC 	4M 	4M 	10	A	-TS
MODEL	INSTRUMENT CONNECTION	PROCESS CONNECTION	LENGTH IN FEET	PROTECTION	OPTIONS
DXC = Capillary	4M = 1/4" Male NPT 4F = 1/4" Female NPT 2M = 1/2" Male NPT	4M = 1/4" Male NPT 4F = 1/4" Female NPT 2M = 1/2" Male NPT	05 = 5 ft. 10 = 10 ft. 20 = 20 ft.	 A = Stainless Steel Armor P = PVC Coated Stainless Steel Armor B = Bare Capillary Tubing (Rare) 	-3M = 3mm ID (10 ft. Max) -TS = Stainless Steel Tag (1-10 Characters) -1M = 1mm ID

?? = Specify,

Length in

FLUSH RINGS

2F = 1/2" Female

8W = 8mm Male

NPT

Welded





- · Used to Flush Process Fluid or Provide Access for Field Calibrations
- · Machined from Solid Bar Stock
- Pressure Ratings Up to ANSI Class 2500
- For Use with W9FF and W9FR Diaphragm Seals (Raised Face)


HOW TO ORDER: Choose options to build a part number. For example: DXFR322S-PM

2F = 1/2" Female

8W = 8mm Male

NPT

Welded



N/A Indicates the option is not available

DIAPHRAGM SEALS

Diaphragm Seals

DIAPHRAGM SEAL OPTIONS

		MS4 MS6 MS8	W5 W6 W7	T5 T6 V5	W9FF W9FR W9RD	W9XT	W9FP	DSTC75	DSTC15 AND LARGER	DSTF05	DSTF75 AND LARGER	DSPP	OR	DXFR
	PULSATION P	ROTEC	TION (ONLY A	VAILABL	E WITH	REOTEM	P PRESSU	RE GAUGE	MOUNTED	TO SEAL)			
-PP	Pulse Plus™	✓	✓	✓	✓	✓	N/A	N/A	✓	N/A	✓	✓	✓	N/A
					DIA	APHRAGI	M COATIN	NG						
-AU	Gold Plated Diaphragm	N/A	✓	N/A	✓	✓	✓	✓	✓	✓	✓	✓	N/A	N/A
-TC	Teflon Coated Diaphragm PTFE	N/A	✓	N/A	✓	✓	✓	N/A	✓	N/A	✓	✓	N/A	N/A
-EP	Electropolished Diaphragm	N/A	N/A	N/A	N/A	N/A	N/A	✓	✓	✓	✓	✓	N/A	N/A
						FIL	LL							
-FW	Fill Port Welded Closed	STD1	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	N/A	N/A
-VF	Fill for Vacuum Service	N/A	✓	N/A	✓	✓	✓	N/A	✓	N/A	✓	✓	N/A	N/A
					CLF	EANING I	AND FINI	SH						
-DG	Degreased, Shipped in Sealed Bag	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	N/A	✓
-ох	Cleaned for Oxygen Service per ASME B40.1	✓	✓	N/A	✓	✓	✓	✓	✓	✓	✓	✓	N/A	✓
-OY	Cleaned for Oxygen Service per MIL-STD-1330D	✓	✓	N/A	✓	✓	✓	✓	√	√	✓	✓	N/A	✓
					PLU	G FOR F	LUSH PC	ORT						
-GS	1/4" SS Plug Installed	STD	STD	STD	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	✓
-JS	1/2" SS Plug Installed	N/A	STD	STD	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	✓
-GH	1/4" Hast C Plug Installed	✓	✓	✓	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	✓
-JH	1/2" Hast C Plug Installed	N/A	✓	✓	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	✓
-GM	1/4" Monel Plug Installed	N/A	✓	✓	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	✓
-JM	1/2" Monel Plug Installed	N/A	✓	✓	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	✓
						TAG O	PTION							
-TS	Stainless Steel Tag (1-10 Characters)								✓					
-TM	Stainless Steel Tag (11-80 Characters)								✓					
-TP	Paper Tag								✓					
					CER	TIFICATI	ION OPTIC	ONS						
-NC	Certificate of NACE Compliance	✓	✓	N/A	✓	✓	✓	N/A	N/A	✓	✓	✓	N/A	✓
-CM	General Material Conformance	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
-MR	MTR - Mill Test Report Certificate	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	N/A	✓
-РМ	PMI - Positive Material Identification Certificate	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	N/A	✓
-HT	Hydrostatic Test per ASME B31.3	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	N/A	N/A
-HL	Helium Leak Test Certificate	✓	✓	N/A	✓	✓	✓	✓	✓	✓	✓	✓	N/A	N/A
✓	✓ Indicates that the option is available on MS4 & MS6.													
		_												

173 PTC-0425 (800) 648-7737 reotemp.com